



TW 300 S

Vacuum motor

As at: 05/12/08 Time:20:24

Pos.	Description	Reference
01	Housing complete, including Items 2+3	030.010 A
02	Pump holder ALU	P...207 B
03	Tumbler switch	P...240
04	Female quick connector 1/4" AG	P...500 B
05	Vacuum motor, 1000 W, OEP	P...870 E
05	Carbon brush (Pair) OEP	P...870 KB
07	Capacitor 0,1uF	P...391
08	Profile sealing, black, OEP	P...971 C
09	Packing ring 115/78x10 mm	P...013
10	Profile, blue, OEP	P...971 G
11	Cable strand with diode	030.367
12	Cable strand with clamp	P...389
13	ale connector NW 8-1/4"	P...525 K
14	Hose clamp 14,5 mm	P...550 A
15	Hose 400 mm	030.021
16	Seal	030.015
17	NDS-X - pump	P...809
18	Seal 42x45 mm	030.014
19	Hose 360 mm	030.020